

# Price List Addendum

EFFECTIVE April 27, 2021



PL2021-GEN-ADD2

## Hydraulic Control Valves

### Excessive Pressure Shut-Off Valve

**VICTAULIC SERIES 979-4  
BERMAD MODEL BC-794-P**

Ductile Iron Body – Epoxy Coated  
Y-Pattern  
SS 316 Tube/Fitting with SS Control  
Accessories  
Pressure up to 400 psi  
Setting Range 15 – 230 psi



Nominal Size  inches	Excessive Pressure Shut-Off							
	Grooved (Standard) 400 psi		Female Threaded 400 psi		Flanged (ANSI 150) 250 psi		Flanged (ANSI 300) 400 psi	
	Victaulic Part Code	Price Each	Victaulic Part Code	Price Each	Victaulic Part Code	Price Each	Victaulic Part Code	Price Each
1½	S01497940G	\$3001.00	S01497940T	\$3470.00	S01497940F	\$3616.00	S014979H0F	\$3643.00
2	S02097940G	3119.00	S02097940T	3533.00	S02097940F	3692.00	S020979H0F	3885.00
2½	S02497940G	4399.00	S02497940T	3576.00	S02497940F	3783.00	S024979H0F	3954.00
3	S03097940G	4575.00	S03097940T	4139.00	S03097940F	4486.00	S030979H0F	4756.00
4	S04097940G	4695.00	–	–	S04097940F	5320.00	S040979H0F	5584.00
6	S06097940G	7900.00	–	–	S06097940F	9104.00	S060979H0F	9441.00
8	S08097940G	12804.00	–	–	S08097940F	12092.00	S080979H0F	12960.00

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

\* Other finishes and valve body materials available upon request.

#### TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

